



Safety Transformers

from 120VA-2000VA 

Wall-Mounted 



Solid Rubber Housing
Series

Volt-Ampere Power	Input* Voltage ~	Output Voltage ~	No.	Sockets Output	Input 	Output 	Order No.
----------------------	---------------------	---------------------	-----	-------------------	--	---	-----------

160 VA	230V	24V	1 CEE 24V 16A 2p.	0,7A	—	3388164
160 VA	230V	24V	2 CEE 24V 16A 2p.	0,7A	—	3388167
350 VA	230V	24V	1 CEE 24V 16A 2p.	1,5A	—	3388168
350 VA	230V	24V	2 CEE 24V 16A 2p.	1,5A	—	3388161



HILDEN

160 VA	230V	42V	1 CEE 42V 16A 2p.	0,7A	—	3388170
160 VA	230V	42V	2 CEE 42V 16A 2p.	0,7A	—	3388169
350 VA	230V	42V	1 CEE 42V 16A 2p.	1,5A	—	3388162
350 VA	230V	42V	2 CEE 42V 16A 2p.	1,5A	—	3388166



HILDEN

500 VA	230V	24V	2 CEE 24V 16A 2p.	2,0A	2 B-Aut. 1p.	3748102
500 VA	230V	42V	2 CEE 42V 16A 2p.	2,0A	—	3788106



REMSCHIED

1000 VA	230V	24V	3 CEE 24V 16A 2p.	4,0A	3 B-Aut. 1p.	3848101
2000 VA -ohne Abb.-	230V	24V	6 CEE 24V 16A 2p.	8,0A	6 B-Aut. 1p.	3848102
1000 VA	230V	42V	3 CEE 42V 16A 2p.	4,0A	3 B-Aut. 1p.	3848103
2000 VA -ohne Abb.-	230V	42V	6 CEE 42V 16A 2p.	8,0A	6 B-Aut. 1p.	3848104



TRIER

– other models on request / subject to modification and errors –

*screw size M